

FULL FACE MASK TR 82 Cod. 112190000

Full Face Mask, Negative Pressure, with threaded connector to EN 148-1 made of:

- Moulded face blank
- Visor, panoramic and wide visibility
- Group that holds in one single body the connection for the filter or
- respirator, the exhale membranes, the inhalation membrane and

the speech device.

- Inner nose cup
- Head harness, five arms
- Neck strap

The mask can be used with negative pressure devices provided with

the same threaded connector to EN 148-1, such as filters, air lines

AC190, etc.



TECHNICAL DATA:

Breathing Resistance:

Test flow	Inhalation mbar		Exhalation mbar	
	Standard	Measured	Standard	Measured
25 cycles/min x 2 l/cycle	≤ 2.5	1.3	≤ 3.0	1.8
30 l/min	≤ 0.5	0.1		
95 l/min	≤ 1.5	0.7		

Inward Leakage

Test gas	Max admitted inw. Leakage %	Measured Penetration %	
		(10 subjects average)	
SF6	0.05	< 0.03	

Limitations for use

The mask cannot be used with positive pressure SCBAs nor with devices not provided with the same connector to EN 148-1.



FULL FACE MASK TR 82 Cod. 112190000

5

MARKING

MATERIALS

Face Blank:	EPDM
Visor:	Polycarbonate
Head harness:	EPDM
Nose Cup:	TPE
Neck strap:	PVC

STORAGE

Store at temperatures between -20 and +50 $^\circ C$ and RH <80 %

WEIGHT

570 g (1,30 lb) approximately

DIMENSIONS/PACKAGING

The mask is delivered in a PE bag into a single carton box, dimensions $230 \times 175 \times 125$ mm (9.05 x 6.89 x 4.92 in. Masks come in a multiple 6 pieces carton, dimensions $470 \times 390 \times 200$ mm (18.50 x 15.35 x 7.87 in)

For more information please check the notes along with the products or the ones published on the website: www.spasciani.com

NOTE: SPASCIANI SpA does not take any responsibility for any possible and unintentional mistake and reserve the faculty of modify materials and technical characteristics of its products at any time and without any notice.